

MicroVantage™ MDP Series

Absolute-Rated (99.98%) High Performance Pleated Polypropylene Filter Cartridges

MicroVantage Ultra Premium Filter Series



- Absolute-Rated Beta 5000 (99.98%) retention efficiency
- 7.0 square feet (0.65 m²) of media surface area per 10" length
 - Maximum throughput and particle retention
 - Longer service life reduces maintenance costs
- 100% polypropylene construction offers wide range of chemical compatibility
- Rigid, molded cage provides greater structural integrity
- Gradient, fixed pore structure increases dirt-holding capacity and resists unloading under high differential pressure
- Manufactured in state-of-the-art white room for high purity
- Complies with Food & Drug Administration's CFR criteria for food & beverage contact
- Meets USP Class VI Biological Test for plastics
- Various end cap configurations available to fit existing housings
- Produced in 10" segments for maximum strength and pleat protection
- Optional preflushed cartridges available for electronic and pharmaceutical applications

Applications

| | |
|-------------------|------------------|
| RO Prefilters | Food & Beverage |
| Process Water | Bottled Water |
| Plating Solutions | Microelectronics |
| Chemicals | Paint/Inks |

Specifications & Operating Parameters

Pore Sizes 0.2, 0.45, 1.0, 3.0, 5.0, 10.0, 20.0, 30.0, 40.0, 50.0 microns

Nominal Lengths 9.75" (24.7 cm), 10" (25.4 cm), 20" (50.8 cm), 30" (76.2 cm), 40" (101.6 cm)

Outside Diameter 2.67" (6.78 cm)

Inside Diameter 1.0" (2.54 cm)

Media Surface Area 7.0 sq. ft. (0.65 m²) per ten inches in length

Gaskets/O-rings

Silicone, Buna N, EPR, Viton, Teflon Encapsulated
Viton (o-rings only)

Materials of Construction

Filter Media: Polypropylene
Outer Cage / Core / End Caps: Polypropylene

Maximum Operating Temperature 176°F (80°C)

Recommended Change-out Differential Pressure
35 psid (2.4 bar)

Maximum Differential (Collapse) Pressure
75 psid @ 70°F (5.2 bar @21°C), 40 psid @176°F (2.8 bar @ 80°C)


Sanitization and Sterilization

Hot water at 175°F (80°C) at 5 psid for 30 minutes
In-line steam at 257°F (125°C) @ 1 psid (0.07 bar) for 30 minutes
Autoclavable at 257°F (125°C) for 30 minutes

FDA and USP Compliance

All filters are manufactured of virgin polypropylene materials. All materials comply with FDA requirements for food contact per CFR Title 21 174.5, 177.1520 and 177.1630. All Components meet USP Class VI Plastics biological reactivity tests.

Flow vs. Pressure Drop



This chart represents typical water flow per 10" cartridge length. The test fluid is water at ambient temperature. Extrapolation for multiple elements tends to be linear, but as flows increase the ΔP of the housing becomes more apparent

Filter Removal Efficiency

| PORE SIZE | BETA 5000 99.98% | BETA 100 99% | BETA 50 98% |
|-------------|---------------------|-----------------|----------------|
| 0.2 micron | 0.20 | 0.10 | 0.05 |
| 0.45 micron | 0.45 | 0.30 | 0.20 |
| 1.0 micron | 1.0 | 0.65 | 0.35 |
| 3.0 micron | 3.0 | 2.5 | 2.0 |
| 5.0 micron | 5.0 | 4.0 | 3.0 |
| 10.0 micron | 10.0 | 8.0 | 7.0 |
| 20.0 micron | 20.0 | 17.0 | 15.0 |
| 30.0 micron | 30.0 | 26.0 | 21.0 |
| 40.0 micron | 40.0 | 34.0 | 28.0 |
| 50.0 micron | 50.0 | 42.0 | 36.0 |

Ordering Guide (Example: MDP1.0-10S3E)

| MDP | 1.0 | 10 | – | S3 | – | E | – |
|--------------|--------------------------------------------------------------------------|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|----------------------------------------------------------------------------------------------------|---|-------------------------------------------------------------------|
| PRODUCT CODE | MICRON | LENGTH | END CAP CONFIGURATION | | GASKET / O-RING | | OPTION |
| MDP | 0.2 0.45 1.0 3.0 5.0 10.0 20.0 30.0 40.0 50.0 | 9.75" 10" 20" 30" 40" | S1 = DOE S3 = 222 w/ Fin End S4 = 222 w/ Flat End S5 = 226 w/ Fin End S6 = 226 w/ Flat End S7 = Internal O-ring with Recessed Plug S9 = Internal O-ring on both ends | | B = Buna N E = EPDM S = Silicone V = Viton T = Teflon encapsulated Viton (O-ring only) | | F = Flushed with 18megohm DI water (Constructed with 10" modules) |



204 N. Link Lane #7
Fort Collins, CO 80524
Office: 970-204-4758 Fax: 970-204-4764
Brandon@IndustrialFilterSource.com
IndustrialFilterSource.com

MicroSentry™, MicroVantage™, Shelco Filters® and the Shelco logo are registered trademarks of the Tinny Corporation. Shelco Filters is a division of the Tinny Corporation.